



In the box

HD 490 PRO |
HD 490 PRO Plus


HD 490 PRO



HD 490 PRO Plus






SENNHEISER



HD 490 PRO | HD 490 PRO Plus

Quick Guide | Kurzanleitung | Guide de démarrage rapide | Guida rapida | Instrucciones resumidas |
Instruções resumidas | Beknopte gebruiksaanwijzing | Krótka instrukcja obsługi | Snabbguide |
Kort vejledning | Πίνακας οδηγιών | Kısa Kılavuz | Краткая инструкция |
快速指南 | 快速使用指南 | クイックガイド | 요약 안내서

Setup



Sennheiser electronic SE & Co. KG

Am Labor 1, 30900 Wedemark, Germany
www.sennheiser.com

Publ. 02/26, 597239/A06


HD 490 PRO



HD 490 PRO Plus




Wearing



Specifications

Acoustic principle	open
Ear coupling	circumaural
Transducer principle	dynamic
Transducer	38 mm
Transmission range	5 Hz to 36,100 Hz (-10 dB)
Sensitivity	105 dB SPL (1 kHz/1 Vrms) 96 dB SPL (1 kHz/1 mW)
Max. sound pressure level	128 dB SPL (1 kHz 5% THD)
Distortion (THD)	<0.2 % (1 kHz, 100 dB SPL)
Impedance	130 Ω (1 kHz)
Power rating	300 mW (100 h, noise IEC 60268)
Temperature range	operation: +0 °C to 50 °C storage: -25 °C to 70 °C
Rel. humidity	operation: 10 to 80 %, not condensing storage: 10 to 90 %
Weight	260 g (w/o cable)

Cleaning



Changing headband | ear cushion | dust protection

